

# SmartDispenser®

## LDAV LOW TORQUE BENCHTOP CA SYSTEM



**SmartDispenser®**  
**Large Dot Any Viscosity**  
 Use this model for dispense volumes between .0009 & 30cc, ideal for large dot dispensing. For use with industrial grade Genius® CA reservoirs and dispense tips.

LDAV-LT-CA


## AirFree® Technology & Cyanoacrylate

Traditional air pressure systems inject moisture filled air into the syringe reservoir activating the cyanoacrylate (CA) cure cycle. AirFree® technology eliminates moisture filled air from the dispensing process protecting the CA formulation. As a secondary safeguard Genius® CA components are made from proprietary plastics that inhibit CA bonding between components.

### Total Cost of Ownership

**AirFree® Technology Adds Profits When Replacing Air Driven Systems**

Cost of ownership, Air vs. AirFree®, one fluid dispenser



**Fishman Corporation** 192 South Street, Hopkinton, MA 01748, United States  
 US & Canada: 800-433-2115 | United Kingdom: 1905 456008 | Europe: +441905 456008  
 Worldwide: 1-508-435-2115 | [www.fishmancorp.com](http://www.fishmancorp.com)

**FISHMAN®**  
 Dispensing Innovation®

# SmartDispenser® LDAV-LT BENCHTOP CA SYSTEM

## LDAV-LT-CA Large Dot Any Viscosity

BARREL SIZE	3CC	5CC	10CC
MIN. VOL. (CC)	.00090	.00158	.00261
MAX. VOL. (CC)	3.0	5.0	10.0
MIN. RATE (CC/SEC)	.023	.040	.065
MAX. RATE (CC/SEC)	.552	.954	1.567
MAX. BACKOFF (STEPS)	500	500	500
MAX. DELAY (SEC)	9.99	9.99	9.99



The SmartDispenser® LDAV-LT-CA (3-10cc) comes with 3-10cc Dispense Gun and 3, 5, 10cc Retaining Rings.


BARREL SIZE	30CC
MIN. VOL. (CC)	.00514
MAX. VOL. (CC)	30.0
MIN. RATE (CC/SEC)	.129
MAX. RATE (CC/SEC)	3.086
MAX. BACKOFF (STEPS)	500
MAX. DELAY (SEC)	9.99



The SmartDispenser® LDAV-LT-CA (30cc) comes with 30cc Dispense Gun and 30cc Retaining Rings.

## Genius® Cyanoacrylate Dispensing Components


Genius® CA dispensing components are designed from a proprietary plastic that prevents the CA from bonding the syringe piston to the syringe barrel and the syringe tip cap to the syringe luer.



## Genius® CA FreeFlow™ Tips and Teflon® Tips


Genius® FreeFlow™ CA Tips and Teflon®\* Tips both prevent CA from clogging the tip during the fluid dispensing process.

\*Teflon is a registered trademark of the Dupont Corporation.




## SMARTDISPENSER® LDAV-LT-CA 3-30CC DISPENSE STARTER KIT CONTENTS

- Foot Pedal
- Keyboard
- Mouse
- Earphone
- Video Camera
- Cisco Wireless Connectivity Device
- Needle Kit
- Manuals
- Power Supply Connection
- Universal Power Supply



# SmartDispenser® LDAH-LT BENCHTOP CA SYSTEM



## SPECIFICATIONS

Usage:	Indoor use
Altitude:	Up to 2000m
Temperature:	0° to 40° C
Maximum Relative:	80% for temperatures up to 31° C decreasing linearly to
Humidity:	50% relative humidity at 40° C
Mains Supply	
Voltage Fluctuations:	Not to exceed ±10%
Installation	
Overvoltage:	Category II
Pollution:	Degree 2, Class 1
Input Voltage:	100-240 VAC 47-63Hz
Max Inrush Current:	3.2A-1.8A
Output Voltage:	5.0VDC
Output Power:	4.6W
Fuse Rating:	1.0A/250 VAC
Initiate Circuit:	Foot Pedal (dry contact) finger switch
Drive Motor:	LDAH-LT-CA 7.5 Degree 48 Steps/Rev
Axial Movement:	LDAH-LT -CA .024 Axial Pitch .0005"/Step
Control Circuitry:	CMOS microprocessor
Interface:	Touch Screen or Keyboard/Mouse
Minimum Dispense Volume:	0.0009ml

## CONTROL UNIT

Size:	5.6 x 9.9 x 6.3in (14.23 x 25.15 x 16cm)
Weight:	4.7lbs (2.13 kg)

## GUN

Length:	7in (17.8cm)
Weight:	6oz (170.1 gr)
Cable Length:	3 feet (91.5cm)

## What makes the SmartDispenser® so smart? The combination of 3 powerful platforms.

### AIR-FREE MANUFACTURING

- One program – worldwide
- Closed-loop feedback
- 6-10X more repeatable than pneumatics
- Volume base numeric dispensing
- Positive displacement via stepper motor
- Firmware proven for over a decade
- Eliminates expensive air compressor
- Designed to integrate into automation systems using PLCs

### WINDOWS 7 NETWORKING

- SD Device to MES System Networking
- Remote programming and lock out
- Real time production data
- Live video feed
- Auto e-mail of unauthorized program changes
- On screen work instruction (audio option)
- Connectivity between SmartDispensers® Desktop, Laptop and Smartphone.
- Video/Audio training and tutorials

### SMARTPHONE FUNCTIONALITY

- Touch screen
- Finger gesturing controls
- MES Networking Apps
- Custom Manufacturing Apps

**Fishman Corporation** 192 South Street, Hopkinton, MA 01748, United States  
 US & Canada: 800-433-2115 | United Kingdom: 1905 456008 | Europe: +441905 456008  
 Worldwide: 1-508-435-2115 | [www.fishmancorp.com](http://www.fishmancorp.com)

**FISHMAN**®  
 Dispensing Innovation®