

# FISHMAN® Barrel Comparison

Why competitors' barrels cannot be used for AirFree™ dispensing.

**Pressure loss destroys repeatability.**

No two barrels are the same. The I.D. and lengths of the Fishman barrel are programmed into the LDS9000 software, thus providing the highest repeatability. Using a competitor's barrel will destroy repeatability due to dimensional differences.

The SurLok™ retaining ring is specifically designed for Fishman barrels. Competitors' barrels are too thick to fit in the locking mechanism. Thus the retaining ring only partially locks, creating safety issues and flexing during the dispense, which destroys repeatability.

