SmartDispenser®

SSDAV High Torque Fiber Optic Automation Intergration Kit(SDIK™)




## AirFree® Technology

The SmartDispenser® SSDAV-HT-FO Benchtop System is ideal for dispensing epoxies for bonding glass fiber to ceramic ferrules. The ProcessControl<sup>2®</sup> program, manages two part epoxies, such as 353ND, and other fiber optic assembly fluids so each ferrule is filled without over flow or air gaps.

Traditional air pressure systems lack the repeatability from one fluid deposit to the next needed for fiber optic connector assembly. AirFree® technology stabilizes the fluid dispensing process providing the highest repeatability when compared to any fluid dispenser.

## **Total Cost of Ownership**

## AirFree® Technology Adds Profits When Replacing Air Driven Systems







## SSDAV-HT-FO-SDIK™ Super Small Dot Any Viscosity

SYRINGES SIZE	3CC	5CC	10CC
MIN.VOL. (CC)	.00011	.00019	.00031
MAX. VOL. (CC)	3.0	5.0	10.0
MIN. RATE (CC/SEC)	.003	.005	.008
MAX. RATE (CC/SEC)	.065	.114	.188
MAX. BACKOFF (STEPS)	500	500	500
MAX. DELAY (SEC)	9.99	9.99	9.99



The SmartDispenser® SSDAV-HT-FO-SDIK™ (3-10cc) comes with 3-10cc Dispense Gun and 3, 5, 10cc Retaining Rings.


SYRINGES SIZE	30CC	
MIN.VOL. (CC)	.00062	
MAX. VOL. (CC)	30.0	
MIN. RATE (CC/SEC)	.015	
MAX. RATE (CC/SEC)	.370	
MAX. BACKOFF (STEPS)	500	
MAX. DELAY (SEC)	9.99	



The SmartDispenser® SSDAV-HT-FO-SDIK™ (30cc) comes with 30cc Dispense Gun and 30cc Retaining Rings.

### **Genius® FO Dispensing** Components

Genius® dispensing components have a thick wall design eliminating flexing and a zero draft assuring smooth flow. Disposable design eliminates the use of harmful cleaning agents such as mek or acetone. The polypropylene reservoir protects assembly workers from coming in contact with harmful assembly fluids. When empty the capped syringe acts as a sealed container making disposal easier and safer.



Hiflow<sup>™</sup> dispense tips are made from 19g (.042"- O.D.) and 20g (.035"- O.D.) which fit perfectly into the fiber optic ferrule's port. The inner diameter of both tips are 15% larger allowing for a higher flow rate of fluid which eases the ferrule filling process.

Worldwide: 1-508-435-2115 | www.fishmancorp.com



#### THE SMARTDISPENSER® SSDAV-HT-FO-SDIK™ **3–30CC DISPENSE STARTER KIT CONTENTS**

- Foot Pedal
- Keyboard
- Mouse
- Earphone
- Video Camera
- Cisco Wireless Connectivity Device
- Needle Kit
- Manuals
- Power Supply Connection
- Universal Power Supply





















# SmartDispenser® SSDAV High Torque Fiber Optic Automation Intergration Kit(SDIK™)



#### **SPECIFICATIONS**

Usage: Indoor use Up to 2000m Altitude: 0° to 40° C Temperature:

Maximum Relative: 80% for temperatures

up to 31° C decreasing

linearly to

50% relative humidity **Humidity:** 

at 40° C

Mains Supply

Voltage Fluctuations: Not to exceed ±10%

Installation

Overvoltage: Category II Pollution: Degree 2, Class 1 Input Voltage: 100-240 VAC

47-63Hz

Max Inrush Current: 3.2A-1.8A Output Voltage: 5.0VDC Output Power: 4.6W

Fuse Rating: 1.0A/250 VAC Initiate Circuit: **PLC Input** 

Drive Motor: SSDAV-HT-FO-SDIK™ .9 Degree

400 Steps/Rev

**Axial Movement:** SSDAV-HT-FO-SDIK™ .24 Axial Pitch

.00006"/Step

Control Circuitry: CMOS microprocessor

Interface: DVI Monitor/Keyboard/Mouse

Minimum Dispense

Volume: 0.00011ml

#### **CONTROL CENTER**

5.6 x 9.9 x 6.3in Size:

(14.23 x 25.15 x 16cm)

Weight: 4.7lbs (2.13 kg)

#### **GUN**

Length: 7in (17.8cm) Weight: 10.6oz (301 gr) 30 feet (914.4cm) Cable Length:

## What makes the SmartDispenser® so smart?

### The combination of 3 powerful platforms.

#### **AIR-FREE MANUFACTURING**

- One program worldwide
- Closed-loop feedback
- 6-10X more repeatable than pneumatics
- · Volume base numeric dispensing
- Positive displacement via stepper motor
- Firmware proven for over a decade
- · Eliminates expensive air compressor
- Designed to integrate into automation systems using PLCs

#### **WINDOWS 7 NETWORKING**

- SD Device to MES System Networking
- · Remote programming and lock out
- Real time production data
- Live video feed
- · Auto e-mail of unauthorized program changes
- On screen work instruction (audio option)
- · Connectivity between SmartDispensers® Desktop, Laptop and Smartphone.
- Video/Audio training and tutorials

#### **SMARTPHONE FUNCTIONALITY**

- Touch screen
- · Finger gesturing controls
- MES Networking Apps
- Custom Manufacturing Apps

