SSDAV High Torque Fiber Optic Automation Intergration Kit(SDIK^M)




AirFree[®] Technology

The SmartDispenser® SSDAV-HT-FO Benchtop System is ideal for dispensing epoxies for bonding glass fiber to ceramic ferrules. The ProcessControl^{2®} program, manages two part epoxies, such as 353ND, and other fiber optic assembly fluids so each ferrule is filled without over flow or air gaps.

Traditional air pressure systems lack the repeatability from one fluid deposit to the next needed for fiber optic connector assembly. AirFree® technology stabilizes the fluid dispensing process providing the highest repeatability when compared to any fluid dispenser.

Total Cost of Ownership

AirFree® Technology Adds Profits When Replacing Air Driven Systems



Fishman Corporation 192 South Street, Hopkinton, MA 01748, United States US & Canada: 800-433-2115 | United Kingdom: 1905 456008 | Europe: +441905 456008 Worldwide: 1-508-435-2115 | www.fishmancorp.com



STATE SPENSER® SSDAV High Torque Fiber Optic Automation Intergration Kit(SDIK^M)

SSDAV-HT-FO-SDIK[™] Super Small Dot Any Viscosity

SYRINGES SIZE	зсс	5CC	10CC
MIN.VOL. (CC)	.00011	.00019	.00031
MAX. VOL. (CC)	3.0	5.0	10.0
MIN. RATE (CC/SEC)	.003	.005	.008
MAX. RATE (CC/SEC)	.065	.114	.188
MAX. BACKOFF (STEPS)	500	500	500
MAX. DELAY (SEC)	9.99	9.99	9.99



The SmartDispenser® SSDAV-HT-FO-SDIK™ (3-10cc) comes with 3-10cc Dispense Gun and 3, 5, 10cc Retaining Rings.

SYRINGES SIZE 30CC

MIN.VOL. (CC)	.00062	
MAX. VOL. (CC)	30.0	
MIN. RATE (CC/SEC)	.015	
MAX. RATE (CC/SEC)	.370	
MAX. BACKOFF (STEPS)	500	
MAX. DELAY (SEC)	9.99	



The SmartDispenser® SSDAV-HT-FO-SDIK™ (30cc) comes with 30cc Dispense Gun and 30cc Retaining Rings.

Genius® FO Dispensing Components

Genius[®] dispensing components have a thick wall design eliminating flexing and a zero draft assuring smooth flow. Disposable design eliminates the use of harmful cleaning agents such as mek or acetone. The polypropylene reservoir protects assembly workers from coming in contact with harmful assembly fluids. When empty the capped syringe acts as a sealed container making disposal easier and safer.

Hiflow[™] dispense tips are made from 19g (.042"- O.D.) and 20g (.035"- O.D.) which fit perfectly into the fiber optic ferrule's port. The inner diameter of both tips are 15% larger allowing for a higher flow rate of fluid which eases the ferrule filling process.



THE SMARTDISPENSER[®] SSDAV-HT-FO-SDIK™ **3–30CC DISPENSE STARTER KIT CONTENTS**

- Foot Pedal
- Keyboard
- Mouse
- Earphone
- Video Camera
- Cisco Wireless Connectivity Device
- Needle Kit
- Manuals
- Power Supply Connection
- Universal Power Supply

















Fishman Corporation 192 South Street, Hopkinton, MA 01748, United States US & Canada: 800-433-2115 | United Kingdom: 1905 456008 | Europe: +441905 456008 Worldwide: 1-508-435-2115 | www.fishmancorp.com



SSDAV High Torque Fiber Optic Automation Intergration Kit(SDIKTM)

SPECIFICATIONS Usage:	Indoor use	
Altitude:	Up to 2000m	
Temperature:	0° to 40° C	
Maximum Relative:	80% for temperatures up to 31° C decreasing linearly to	
Humidity:	50% relative humidity at 40° C	/
Mains Supply Voltage Fluctuations:	Not to exceed ±10%	
Installation Overvoltage:	Category II	
Pollution:	Degree 2, Class 1	
Input Voltage:	100-240 VAC 47-63Hz	
Max Inrush Current:	3.2A-1.8A	
Output Voltage:	5.0VDC	
Output Power:	4.6W	
Fuse Rating:	1.0A/250 VAC	
Initiate Circuit:	PLC Input	
Drive Motor:	SSDAV-HT-FO-SDIK™	.9 Degree 400 Steps/Rev
Axial Movement:	SSDAV-HT-FO-SDIK™	.24 Axial Pitch .00006"/Step
Control Circuitry:	CMOS microprocessor	r
Interface: DVI Monitor/Keyboard/Mo		d/Mouse
Minimum Dispense Volume:	0.00011ml	

CONTROL CENTER

Size:	5.6 x 9.9 x 6.3in (14.23 x 25.15 x 16cm)
Weight:	4.7lbs (2.13 kg)

GUN

Length:	7in (17.8cm)
Weight:	10.6oz (301 gr)
Cable Length:	30 feet (914.4cm)

What makes the SmartDispenser® so smart? The combination of 3 powerful platforms.

AIR-FREE MANUFACTURING

- One program worldwide
- Closed-loop feedback
- 6-10X more repeatable than pneumatics
- Volume base numeric dispensing
- Positive displacement via stepper motor
- Firmware proven for over a decade
- Eliminates expensive air compressor
- Designed to integrate into automation systems using PLCs

- WINDOWS 7 NETWORKING
- SD Device to MES System Networking
- Remote programming and lock out
- Real time production data
- Live video feed
- Auto e-mail of unauthorized program changes
- On screen work instruction (audio option)
- Connectivity between SmartDispensers® Desktop, Laptop and Smartphone.
- Video/Audio training and tutorials

SMARTPHONE FUNCTIONALITY

- Touch screen
- Finger gesturing controls
- MES Networking Apps
- Custom Manufacturing Apps



US & Canada: 800-433-2115 | United Kingdom: 1905 456008 | Europe: +441905 456008 Worldwide: 1-508-435-2115 | www.fishmancorp.com

Fishman Corporation 192 South Street, Hopkinton, MA 01748, United States