
# MDAV LOW TORQUE BENCHTOP CA SYSTEM




# AirFree® Technology & Cyanoacrylate

Traditional air pressure systems inject moisture filled air into the syringe reservoir activating the cyanoacrylate (CA) cure cycle. AirFree® technology eliminates moisture filled air from the dispensing process protecting the CA formulation. As a secondary safeguard Genius® CA components are made from proprietary plastics that inhibit CA bonding between components.

## **Total Cost of Ownership**

### AirFree® Technology Adds Profits When Replacing Air Driven Systems







# **Smart**Dispenser® MDAV-LT BENCHTOP CA SYSTEM

### **MDAV-LT-CA Medium Dot Any Viscosity**

BARREL SIZE	3CC	5CC	10CC
MIN.VOL. (CC)	.00045	.00079	.00131
MAX. VOL. (CC)	3.0	5.0	10.0
MIN. RATE (CC/SEC)	.011	.020	.033
MAX. RATE (CC/SEC)	.267	.477	.783
MAX. BACKOFF (STEPS)	500	500	500
MAX. DELAY (SEC)	9.99	9.99	9.99



The SmartDispenser® MDAV-LT-CA (3-10cc) comes with 3-10cc Dispense Gun and 3, 5, 10cc Retaining Rings.

MIN.VOL. (CC)	.00257	
MAX. VOL. (CC)	30.0	
MIN. RATE (CC/SEC)	.064	
MAX. RATE (CC/SEC)	1.543	
MAX. BACKOFF (STEPS)	500	
MAX. DELAY (SEC)	9.99	



The SmartDispenser® MDAV-LT-CA (30cc) comes with 30cc Dispense Gun and 30cc Retaining Rings.


#### **Genius® Cyanoacrylate Dispensing Components**


Genius® CA dispensing components are designed from a proprietary plastic that prevents the CA from bonding the syringe piston to the syringe barrel and the syringe tip cap to the syringe luer.

### **Genius® CA FreeFlow™ Tips** and Teflon® Tips

Genius® FreeFlow™ CA Tips and Teflon®\* Tips both prevent CA from clogging the tip during the fluid dispensing process.

\*Teflon is a registered trademark of the Dupont Corporation.







#### **SMARTDISPENSER® MDAV-LT-CA 3-30CC DISPENSE STARTER KIT CONTENTS**

- Foot Pedal
- Keyboard
- Mouse
- Earphone
- Video Camera
- Cisco Wireless Connectivity Device
- Needle Kit
- Manuals
- Power Supply Connection
- Universal Power Supply



















# **Smart**Dispenser® MDAV-LT BENCHTOP CA SYSTEM



#### **SPECIFICATIONS**

Usage: Indoor use
Altitude: Up to 2000m
Temperature: 0° to 40° C

Maximum Relative: 80% for temperatures up to 31° C decreasing

linearly to

Humidity: 50% relative humidity

at 40° C

Mains Supply

Voltage Fluctuations: Not to exceed ±10%

Installation

Overvoltage: Category II

Pollution: Degree 2, Class 1
Input Voltage: 100\_240 VAC

47-63Hz

Max Inrush Current: 3.2A-1.8A
Output Voltage: 5.0VDC
Output Power: 4.6W

Fuse Rating: 1.0A/250 VAC

Initiate Circuit: Foot Pedal (dry contact)

finger switch

Drive Motor: MDAV-LT-CA 3.75 Degree

96 Steps/Rev

Axial Movement: MDAV-LT-CA .024 Axial Pitch

.00025"/Step

Control Circuitry: CMOS microprocessor

Interface: Touch Screen or Keyboard/Mouse

Minimum Dispense

Volume: 0.00045ml

**CONTROL UNIT** 

Size: 5.6 x 9.9 x 6.3in

(14.23 x 25.15 x 16cm)

Weight: 4.7lbs (2.13 kg)

GUN

 Length:
 7in (17.8cm)

 Weight:
 6oz (170.1 gr)

 Cable Length:
 3 feet (91.5cm)

# What makes the SmartDispenser® so smart?

The combination of 3 powerful platforms.

#### **AIR-FREE MANUFACTURING**

- One program worldwide
- · Closed-loop feedback
- 6-10X more repeatable than pneumatics
- Volume base numeric dispensing
- · Positive displacement via stepper motor
- Firmware proven for over a decadeEliminates expensive air compressor
- Designed to integrate into automation systems using PLCs

#### WINDOWS 7 NETWORKING

- SD Device to MES System Networking
- Remote programming and lock out
- Real time production data
- Live video feed
- · Auto e-mail of unauthorized program changes
- On screen work instruction (audio option)
- Connectivity between SmartDispensers® Desktop, Laptop and Smartphone.
- Video/Audio training and tutorials

#### **SMARTPHONE FUNCTIONALITY**

- Touch screen
- Finger gesturing controls
- MES Networking Apps
- Custom Manufacturing Apps

